


サビ 錆に強いステンレスドライバー

5%のNaClの水溶液に30秒浸漬後、室内放置60H



暗い所でハンドルが発光します



暗いところで光を放つ特殊蓄光樹脂を使用。暗いところでもすぐにドライバーを認識できます

直射日光10分照射で24H発光効果有

No.1505 ステンレス蓄光ドライバー レギュラータイプ



SIZE	A	B	C	D	E	F	G	Box	Barcode
5.5×75	5.5	0.75	No.1	75	5.5	175	29	12	342111
6×100	6.0	0.95	No.2	100	6.3	210	32	12	342128
8×150	8.0	1.10	No.3	150	8.0	270	35	6	342135



1×75			No.1	75	5.5	175	29	12	342210
2×100			No.2	100	6.3	210	32	12	342227
3×150			No.3	150	8.0	270	35	6	342234

No.1505 ステンレス蓄光ドライバー スタービータイプ



SIZE	A	B	C	D	E	F	G	Box	Barcode
6×35	6.0	0.9	No.1	35	6.0	80	33	12	342319
2×35			No.2	35	6.0	80	33	12	342326